

Dermalase IPL Specifications

INDICATIONS

SR: Skin-Rejuvenating. It is used for eliminating wrinkles, enhancing skin elasticity, evens out pigmentation, age spots, sun-induced freckles, vascular indications, spider veins, and more.

HR: Hair-Removal. It is used for removing undesired hair of limbs, lips & face by rapid destruction of hair follicles.

SYSTEM FEATURES

Broader fluence: 5-50 Joules

Designed with 2 handles ports: easy to use, no need to change handles between treatments

Super large HR spot size: 16 x 57mm, the average one is only 8 x 40mm. this large spot size will make the treatment more efficient and reduce treatment time in half. SR spot size: 8 x 34mm

Screen: friendly touch-screen interface for the operator

SPECIFICATIONS

Light source: Intense Pulsed Light

Wavelength: SR 560-1200nm. HR 690-1200nm

Transfer system: Crystal light guide

Safety Category: Class III, type B

Pulse width: 20-149.7 msec

Pulse delay: 5-60 msec

Pulse per train (pulse-in-pulse) 1p/s pulse per second

Pulse rate: 33 Hz

The light mouth dimension: 8mm 34mm/16mm 57mm, error 0.2mm

Cooling system: Semiconductor refrigerator, air cooled plus water cooled

Dimensions: (L x W x H) 490*525*1050mm

Weight: (NW) 35kg

Fuse specifications: 5 - 20 10A

Input power: 600W (steady state)

Power: AC 120V, 50HZ

The Dermalase IPL from

NU BODY

SAFE • EFFECTIVE • AFFORDABLE

604-788-3413

www.nubodyequipment.com

